

# Bertrandt Powertrain Solution Center Product datasheeds BPSC

Christian Eberle | 15.02.2022

## The entire world in one place

Whether battery-electric, hybrid or internal combustion engine drive - with the **Bertrandt Powertrain Solution Center** in Wolfsburg or Munich, we offer **validation**, certification and real-driving emissions tests for all drive concepts - in accordance with legal and/or customer-specific requirements.





#### **Bertrandt Powertrain Solution Center**



2 all-wheel A/C roller test benches with altitude chamber



6 all-wheel A/C chassis dynamometers



2 chambers for Sealed Housing for Evaporative Determination measurements (SHED)









# All-wheel A/C roller test stands with altitude chamber

 $\underline{} \otimes \underline{} \otimes \underline{}$ 



-☆: 🖟 Temperature range:

- Speed:
- **世上** HV charging infrastructure:
- Altitude simulation:



Sunlight simulation:



**Emission measurement technology:** 

From -25 °C to +45 °C

Up to 300 km/h

550 kW

22KW (400 kW\*)

4200m (5.000 m\*) [↑ 3m/s | ↓ 6m/s] Irradiable area: 7 m x 2.5 m

AVL Slim Line



Office area

climate equipped cha dynamometers with altitude chamber -25 °C/+45 °C

# Technical data All-wheel A/C roller dynamometers with altitude chamber

# Roll Performance 8-8-

Manufacturer	AVL customs
Туре	AVL ROADSIM 48" MIM 4x2
Roller diameter	48" parting roll
Power	2 x 360 kW
Flywheel mass range (1axis)	454 kg 4.250 kg
Flywheel mass range (2 axis)	800 kg 8.500 kg
Flywheel masses	Electrically simulated
Max. Axle load	2.500 kg
Max. Speed	300 km/h
Axle distance	1.800 – 4.500 mm
Track width	900 mm Inner edges of tires 2.030 mm Outer edges of tires
Vehicle holder systems	<ul> <li>Vehicle weight max. 3,500 kg</li> <li>Maximum acceleration 10 m/s<sup>2</sup></li> <li>Maximum tractive force 30,000 N</li> </ul>

# **Emission Measurement**



Manufacturer CVS plant	AVL Emission Test Systems, Typ CVS AL LE
Measuring principle	Critical Flow Venturi (CFV) / 4 CFV
Maximum flow rate	40 nm³/min
Options	<ul> <li>Isolated and heated;</li> <li>Tail Pipe Pressure Control</li> <li>Dilution Air</li> <li>Flow measurement</li> </ul>
Manufacturer exhaust gas measuring system	AVL Emission Test Systems, Type AMA SL D1
Analyzer CO2 /CO/NOx	IRD SL/IRD SL/CLD SL
Analyzer THC/CH4/Tunnel THC	Twin FID SL
Special measurement technology	<ul> <li>2 x 3 lines raw exhaust gas measurement</li> <li>7 x FTIR (raw exhaust gas) / 4 x Micro Soot</li> <li>4 x Opacimeter</li> <li>AVL Particle Sampling System</li> <li>AVL Particle Counter</li> <li>AVL Filter Weighing Robot FWR 585</li> <li>Hioki 3390 current power meter</li> <li>Quantum cascade laser for the measurement of nitrous oxide (N2O)</li> </ul>

# Technical data All-wheel A/C roller dynamometers with altitude chamber

Height simulation 📈

- Altitudes from ambient Altitude 4200m
  - 5000 m in progress
- Exhaust gas measurement via the CVS up to an altitude of 3,000 m
- Pressure adjustment [↑ 3m/s | ↓ 6m/s]

# Temperature range

- From -25 °C to + 45 °C
- Adjustable test stand humidity

## **Traction blower**

- Manufacturer: AVL
- Type: RDE & SC03 Blower

# HV charging infrastructure

- 16 x 22 kW charging station
- 1 x 160 kW outdoor charging station
- In progress: 8 x 400 kW charging station
- Discharge and range testing for BEVs
- Adaptation of SOC HV storage of BEV vehicles
- Existing safety concept for operation of PHEV and BEV vehicles, special extinguishing equipment (fire blanket) and fire extinguishers with additives

# Sunlight simulation

- Manufacturer: BF Engineering
- Maximum with up to 94 kW power
- Floodlights: 24 x BF SUN 4.000 W
- Daylight lamps: Type Osram HMI 4.000 W DXS
- Motorized shading: tunnel drive/cloud simulatable
- irradiable area 7 x 2,5 m

# Special measurement technology

- 2 x 3 lines raw exhaust gas measurement
- 7 x FTIR (raw exhaust gas) / 4 x Micro Soot
- 4 x Opacimeter
- AVL Particle Sampling System
- AVL Particle Counter
- AVL Filter Weighing Robot FWR 585
- Hioki 3390 current power meter
- Quantum cascade laser for measurement of nitrous oxide (N2O)
- Driving robot Stähle SAP 2000 for computercontrolled driving of vehicles on test benches
- 2 lines activated carbon filter loading station for the legally required conditioning of AKF





### **Bertrandt Powertrain Solution Center**



2 all-wheel A/C roller test benches with altitude chamber



6 all-wheel A/C chassis dynamometers



- 2 chambers for Sealed Housing for Evaporative Determination measurements (SHED)
- Special measurement technology







## All-wheel A/C chassis dynamometers





Temperature range:



Speed:

# 비고 HV charging infrastructure:



**Emission measurement technology:** 

360 kw

From -7 °C to +40 °C

To 250 km/h

22KW (400 kW\*)

AVL Slim Line



# Technical data all-wheel A/C chassis dynamometers

# Roll Performance

Manufacturer	AVL customs
Тур	AVL ROADSIM 48" MIM 4x2
Roller diameter	48" parting roll
Power	2 x 210 kW
Flywheel mass range(1 axis)	454 kg 4.250 kg
Flywheel mass range ( 2axis)	750 kg 7.000 kg
Flywheel masses	Electrically simulated
Max. Axle load	2.500 kg
Max. Speed	250 km/h
Axle distance	1.800 – 4.500 mm
Track width	900 mm Inner edges of tires 2.030 mm Outer edges of tires
Vehicle systems	<ul> <li>Vehicle weight max. 3,500 kg</li> <li>Maximum acceleration 10 m/s<sup>2</sup></li> <li>Maximum tractive force 30,000 N</li> </ul>

### Emission Measurement



Manufacturer CVS plant	AVL Emission Test Systems, Type CVS AL LE
Measuring principle	Critical Flow Venturi (CFV) / 4 CFV
Maximum flow rate	40 nm³/min
Options	<ul> <li>Isolated and heated;</li> <li>Tail Pipe Pressure Control</li> <li>Dilution Air</li> <li>Flow measurement</li> </ul>
Manufacturer exhaust gas measuring system	AVL Emission Test Systems, Type AMA SL D1
Analyzer CO2 /CO/NOx	IRD SL/IRD SL/CLD SL
Analyzer THC/CH4/Tunnel THC	Twin FID SL
Special measurement technology	<ul> <li>AVL Particle Sampling System</li> <li>AVL Particle Counter</li> <li>AVL Filter Weighing Robot FWR 585</li> <li>Hioki 3390 current power meter</li> <li>Quantum Cascade Laser for the Measurement of Nitrous Oxide (N2O)</li> </ul>

# Technical data all-wheel A/C chassis dynamometers

#### Special Measurement



- AVL Particle Sampling System
- AVL Particle Counter
- AVL Filter Weighing Robot FWR 585
- Hioki 3390 current power meter
- Quantum cascade laser for the measurement of nitrous oxide (N2O)
- Driving robot Stähle SAP 2000 for computer-controlled driving of vehicles on test benches
- 2 lines activated carbon filter loading station for the legally required conditioning of AKF

#### **Traction blower**

- Manufacturer: AVL
- Type: RDE & SC03 Blower
- Max. Air speed 0.3 m<sup>2</sup> @160 km/h

#### **Temperature range**

- From -7  $^{\circ}$ C to + 40  $^{\circ}$ C
- Adjustable test bench humidity (3/14.2 g/kg dry air (±1 g/kg)

#### HV- charging infrastructure



- 16 x 22 kW charging station
- 1 x 160 kW outdoor charging station
- In progress: 8 x 400 kW charging station
- Discharge and range testing for BEVs
- Adaptation of SOC HV storage of BEV vehicles
- Existing safety concept for operation of PHEV and BEV vehicles, special extinguishing equipment (fire blanket) and fire extinguishers with additives





### **Bertrandt Powertrain Solution Center**



2 all-wheel A/C roller test benches with altitude chamber



6 all-wheel A/C chassis dynamometers



- 2 chambers for Sealed Housing for Evaporative Determination measurements (SHED)
- Special measurement technology







# Two cambers for SHED measurements

# Sealed Housing for Evaporative Determination measurements (SHED)

Manufacture/type:

**E** 

**Dimensions full size:** Inside (W x H x D): AVL VV/VT-SHED

2.200 x 2.700 x 6.600 mm; about 48 m<sup>3</sup> volume



**Dimensions magnum:** Inside (W x H x D):

3.500 x 3.600 x 8.700 mm; about 96 m<sup>3</sup> volume



15 – 60°C

#### SHED chambers

| Conditioning area | +23 °C



#### **Technical data SHED measurements**

#### **Measurements**

- Fulll Size SHED Dimensions (Inside) (W x H x D): 2200 x 2700 x 6600mm
- Magnum SHED Dimensions (Inside) (W x H X D): 3500 x3600 x8700mm
- Measurement component : THC

#### **Temperature range**

- Temperature chamber: test operation 15 45 °C, bakeout phase max. 60 °C
- Temperature control accuracy ±0.5 °C
- Temperature dynamics : 0.5 -1°C/ min (between 20 -40 °C)

#### Volume

- Full Size SHED volume: about 48 m<sup>3</sup>
- Magnum Shed volume: about 96 m<sup>3</sup>

# AVL VV/VT-SHED

#### attachment

- Used to determine gaseous ab: Diurnal & Hot Soak fuel emissions from motor vehicles or parts thereof, according to legal requirements (e.g. EPA Title 40 Part 80 and Part 86 and EU Regulation 715/2007)
- Temperature chamber for measurement of evaporative emissions / VV/VT-SHED
- Inspection and testing of all kinds of vehicles (e.g. automobiles, motorcycles, scooters, etc.) but also off-road equipment (lawn mowers, chainsaws, etc.)
- In special cases: Testing of tank superstructures, individual components or modules
- The included application package covers with its ready-to-use configurations as well as the subsequent data processing and evaluation routines the following currently valid legal test procedures and standards Test Procedure (ECE R83, Annex 7, Type IV Test)

#### **Test sequences & standard**

- Diurnal Test Procedure (EPA CFR 40 §86.133-96)
- Hot Soak Test (EPA CFR 40 §86.138-96)
- ORVR Refueling Test Procedure (EPA CFR 40 §86.150-98)
- DBLT Diurnal Breathing Loss Test (EPA CFR 40 §86.133-90; Brazil)
- Bleed Emission Test Procedure (Passive SHED)
- EPA CFR 40 §1066 Subpart J (referring to EPA §86)
- CARB CCR 13 § 1976 (referring to EPA §86)
- CHINA Beijing 6 (referring to EPA §86)
- INDIA (referring to ECE R83 Type IV Test)
- JAPAN JASIC 11-3-49 §8f (referring to ECE R83, Type IV Test)



### **Bertrandt Powertrain Solution Center**



2 all-wheel A/C roller test benches with altitude chamber



6 all-wheel A/C chassis dynamometers



2 chambers for Sealed Housing for Evaporative Determination measurements (SHED)









# **Real Driving Emissions (RDE) workshops**



Installation/attachment Portable Emission Measurement (PEMS) measurement technology



**4 lifting platforms** 



Modern workshop equipment



Customer conversions / individual vehicle conversions





# You can find more information on our website

 $\rightarrow$ Your request by email:

# anfragen@bertrandt.com

→ https://www.bertrandt.com/bpsc/

- technical specifications
- all solutions and services
- background information

